







## **TYPE SKD330, SK330, SKD30**

### Assembling information RAMPA®-Inserts type SKD330 / SK330 / SKD30


The values in the table are applicable exclusively to RAMPA®-Inserts as listed below.

RAMPA®-Inserts | Type: SKD330, SK330, SKD30









- L —
- L -

Outer-Ø **Threadsize** Steel **Hex Drive D** (mm) **d** (mm) zinc-plated Μ4 4 10 М5 5 12 М6 6 14 **M8** 8 18,5 M10 10

<sup>\*1</sup> For RAMPA inserts type SK330 applies: We hereby inform you according to Article 33 - REACH, that this article contains the following substance identified as SVHC: Lead (Pb); CAS: 7439-92-1 Date of Admission: 27.06.2018









# **TYPE SKD330, SK330, SKD30**

### Assembling information RAMPA®-Inserts type SKD330 / SK330 / SKD30


#### **Preparatory work:**

#### **Preparatory work:**

- Outer-Ø D ≥ 12mm
- t= 2mm
- Tolerance range ttol1 D ≥12mm=+0,5mm
- Outer-∅ D ≤ 10mm
- t= 1mm
- Tolerance range ttol1 D ≤10mm=-0,5mm

#### Example: RAMPA®-Inserts | Type: SKD330 Art. No.: 420615001

- Standard pre-drill- $\emptyset$  =D t = d  $\rightarrow$  12mm 2mm = 10mm
- Max./min. allowed- $\emptyset = D (t-(t_{tol,1})) = d \rightarrow 12mm (2mm (+0,5mm)) = 10,5mm$



(The same applies to the inserts type SK330 without collar)

- Always use the minimum pre-drill-Ø for wood and wood materials.
- If any problem occurs during assembling process, the pre-drill-Ø can be adapted to the tolerance range ttol. 1 as mentioned above.
- As far as possible, drills in hardwoods (density < 500kg/m3) or plastics should have a countersink of s=min. 0,3mmx45°.
- Due to the very homogeneous mechanical properties, in plastics the highest permitted pre-drill-Ø can be used.
- The pre-drill-depth should be tmin = total length of inserts + 2mm (avoiding breaking through material).







# **TYPE SKD330, SK330, SKD30**

### Assembling information RAMPA®-Inserts type SKD330 / SK330 / SKD30

Example: RAMPA®-Inserts | Type: SKD330 Art. No.: 420615001

- Outer-Ø D = 10mm
- Counterbore- $\emptyset$  (d<sub>1</sub>) = D + (2 x s)  $\rightarrow$  10mm + (2 x 0,3mm) = 10,6mm

Make sure that the pre-drilled hole is clean or free of chips.

#### Assembling:

The **RAMPA®-Inserts** must be completely put on the hexagon bit-socket (fig. 2) before starting the assembling process. For avoiding bulges, the inserts must be assembled in the pre-drilling with slight pressure (fig. 3). During processing, the screw-in speed should be increased step by step in order to have the best possible control over the screw-in depth.

- ⇒ Assembling-speed =
  - SKD330: max. 175min<sup>-1</sup>
  - SKD30: max. 250min<sup>-1</sup>
  - SK330: max. 100min<sup>-1</sup>
- The switch-off range of the assembling torque can be found in the relevant product data sheet from RAMPA GmbH & Co. KG. The indicated cut-off torques are guides that might vary.

Excessive cut-off torque can cause damage to the workpiece!




Figure 2 (The same applies to the inserts type SK330 without collar)




Figure 3 (The same applies to the inserts type SK330 without collar)